



Fisherbrand™ Traceable™ has your monitoring needs covered

Simple, digital reporting

Designed to evolve how you monitor data.

MIN/MAX Memory

Manually monitor readings with minimum/maximum memory

USB Data Retrieval

Download data from device to USB flash drive

WI-FI/Ethernet Connected

Real-time, remote monitoring—receive alerts on mobile device or email



MIN/MAX Monitoring

- Minimum/Maximum Memory
- High Low Alarms

USB Data Logging

- Log Data Continuously
- Download Memory Data to PC

Cloud Service Monitoring

- 24/7 Remote Monitoring
- Built in VFC Reporting

	Traceable™ Min/Max Memory	Traceable™ Excursion-Trac™ USB Data Logging	TraceableLIVE™ Cloud Service (Wi-Fi or Ethernet)
DATA STORAGE	Minimum/Maximum (until cleared)	2 years (resettable)	Unlimited cloud storage
USER INTERFACE	Local display	Local display	Local display, Web, smartphone
ALARMS	Audible, visual	Audible, visual	Email, SMS text, Push notification, audible, visual
DATA OUTPUT	None (pen & paper)	USB data stick to Excel file	Real-time graphs, reports, alarm history, statistics, audit trail, cal due notice
EMAIL/TEXT ALERTS	✗	✗	✓
NIST-TRACEABLE CALIBRATION CERT	✓	✓	✓
VACCINE FOR CHILDREN COMPLIANT	✗	✓	✓
21 CFR 11 COMPLIANT OPTIONS	✗	✗ (available on Memory-Loc options -see fishersci.com)	✓
APPLICATION	Cat. No.	Cat. No.	Cat. No.
FRIDGE/FREEZER features buffered glycol bottle probe	14-650-103	15-081-123	Wi-Fi: 15-079-615 Ethernet: 15-079-704
ULTRA-LOW FREEZER -80°C features stainless-steel probe	15-081-108	15-079-624	Wi-Fi: 15-079-626 Ethernet: 15-079-705

In the United States

Order online: fishersci.com
 Fax an order: 1-800-926-1166
 Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca
 Fax an order: 1-800-463-2996
 Call customer service: 1-800-234-7437

