

Lab Essentials from Bel-Art – SP Scienceware

Catalog No. Description

All Around the Laboratory

11-999-18	Labmat™ Bench Liner – 50 foot roll, white (1)
03-411-758	Round Lead Ring Flask Weight, Fits 500-2000ml Flasks (2)
22-260-103	Open-C Lead Ring Weight, Fits 250-1000mL Flask (3)
11-394-299	Clavies® Autoclave Gloves, 13" gauntlet (4)
08-647-730	Hot Hand® Mitt, lime green (5)
08-647-729	Hot Hand® Mitt, sky blue (6)
22-029064	Foil Squares, 8 x 8", Box of 100 (7)

No-Wire™ Tube & Bottle Racks - Autoclavable, Polypropylene

14-791-5B	13-16mm Bottle & Vial Rack, 30 place, White
22-269947	10-13mm Test Tube Rack, 90 place, White (8)
03-411-770	15-16mm Test Tube Grip Rack, 60 place, Can be submerged in a water bath (9)

Sterile Sampling - individually wrapped, FDA grade polystyrene tools

14-429B	Sterileware® ½ Tsp. Sampling Spoon (10)
14-358-20	Sterileware® Sampling V-shaped 6" Spatula, 9" total length (11)
14-512-205	Sterileware® Earth-Friendly 1001 Sticks (12)
14-241-10B	Sterileware® 4oz. Sampling Scoops, flat bottom for use as weigh boats (13)
14-375-612	Sterileware® Sense-able Scoops®, 2oz. Sampling Scoops-Blue (14)

Biohazard Waste Disposal

22-279178	Biohazard Disposal Carton, autoclavable, printed graphics in English, Spanish, French, German (15)
11-394-303	Bench-Top Biohazard Bag Holder Cover, 5L x 3½W x 5⅝"H (16)
01-815-2	Bench-Top Biohazard Bag Holder, 3⅜L x 5W x 8½"H (16)
03-410-591	Bench-Top Biohazard Bags, 8½L x 11"W (16)

Safety-Vented 4 Color Wash Bottles NFPA Diamond, Pictogram instructions for universal understanding

03-411-720	FGHS Labeled Safety-Vented Acetone Wash Bottles; 500ml (16oz) (17)
03-411-734	GHS Labeled Safety-Vented Assorted Wash Bottles; 500ml (16oz)
03-411-730	GHS Labeled Safety-Vented Sodium Hypochlorite (Bleach) Wash Bottles; 500ml (16oz) (18)
01-189-100	SP Scienceware® Trigger Sprayers with 53mm Adapters (19)




Pitchers, Cylinders & Beakers - Autoclavable, Polypropylene

16-800-541	150mL Beaker – Graduated every 25mL (20)
22-261438	1000mL Polypropylene Cylinder – Roll-proof, easy-to-read with a large spout (21)
22-171124	3000mL Pitcher – Graduated every 50mL (22)

Pipetting Supplies

03-410-537	Fast Release Pipette Pump™ III (23)
10-987-051	Bulb Pipettor, can be autoclaved (24)
22-261824	Automatic Burette, 25mL capacity, 1000mL reservoir (25)
12-948-118	Roxy M™ Repeating Pipettor (26)
12-948-101	Roxy M™ Non-Sterile Tips, 0.5mL (26)
12-948-103	Roxy M™ Non-Sterile Tips, 2.5mL (26)





Lab Essentials from Bel-Art – SP Scienceware

Catalog No. Description

Easy, Secure, Color-coded Labeling. 6 Vivid Colors, -112°F to 176°F for 24 hours

03-411-601	Write-On™ Label Tape – White, 3/4", 15 Yards, 1" core (27)
03-411-628	Write-On™ Label Tape – White, 3/4", 60 Yards, 3" core (27)
03-411-625	Write-On™ Label Tape – Orange, 3/4", 40 Yards, 3" core (27)
03-411-604	Write-On™ Label Tape – Yellow, 3/4", 15 Yards, 1" core (27)
03-410-486	Tape Dispenser – holds up to 5 rolls of tape, steel serrated cutting edge (28)

Magnetic Stirring – Spinbar® Teflon® covered bars for excellent performance everytime!

10-987-044	Portable, Battery-operated Magnetic Stirrer – 900 RPM, mix up to 1 liter with stirring bars up to 1" (29)
14-513-59	Fisherbrand 1" x 5/16" Octagon with pivot ring (30)
22-215079	1" x 5/16" Cylinder with pivot ring
22-331462	Octagon 12-pack, assorted size bars with pivot rings
22-269746	Spinbar Magnetic Stirring Bar Retriever; 18 in (31)

Magic Touch™ 2 Icewares – Durable, non-sweating, foam with superior insulation properties

11-999-064	Midi Ice Pan w/Lid – 4L, Red (32)
11-999-054	Ice Bucket w/Lid – 2.5L, Blue (33)

Durable Tubing Clamps

05-832	Plastic Jaw Style Tubing Clamps; Fits tubing size up to 0.82mm (1/32") wall thickness (34)
22-087957	Acetal Mid-Range Plastic Tubing Clamps; 15-position stepped adjustment; fits tubing from 3.2 to 11mm (1/8 to 7/16") O.D. (35)

Water/Liquid Sampling

22-111153	Dipper with 3' handle and 500ml (16oz) HDPE cup (36)
22-261785	Bellows sampler, 50ml, 19.5" long (37)

Fume Hood: Safely vent noxious or potentially hazardous fumes and dust

03-421-123	Clear View Fume Hood 1 x 1, Polycarbonate with 3 position sash (38)
------------	---

Spinbar® Magnetic Stirring Bars

22-271825	Octagon Spinbar® Magnetic Stirring Bars, 1 x 3/8" (39)
22-271841	Octagon Spinbar® Magnetic Stirring Bars, 2 x 3/8" (40)
22-331488	Octagon Spinbar® Magnetic Stirring Bars, 3 x 1/2" (41)
22-271783	Micro (Flea) Spinbar® Magnetic Stirring Bars, 10 x 3 mm (42)

Desiccation – Low Humidity Storage

08-594-15B	Space Saver Vacuum Desiccator, 19.7 inner diameter x 26cmH. Polycarbonate top with polypropylene bottom, will hold a full vacuum for 24 hours (43)
08-647-658	Secador® Standard Desiccator 2.0, 1.16 cu. ft. volume, 99% UV light blocking (44)
08-594-19	Desi Can™ Reusable Desiccant, canister cartridge can be regenerated in an oven for unlimited life (45)

Contact us today:

In the United States

Order online: fishersci.com

Fax an order: 1-800-926-1166

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Fax an order: 1-800-463-2996

Call customer service: 1-800-234-7437