

Fisherbrand Cell Culture Plasticware

The Collection is Growing

The new line of Fisherbrand™ Tissue-Culture-Treated Plasticware includes a full selection of flasks, dishes and multi-well plates. They're made from 100% virgin polystyrene, manufactured in a Class 100,000 cleanroom, treated to enhance attachment of adherent cell lines, and gamma sterilized to an SAL of 10⁻⁶.

Features

- Conform with USP Class VI and ISO 10993-5 standards
- Non-pyrogenic and non-cytotoxic
- DNase and RNase free
- BSE and TSE free
- Lot numbers appear on case labels, inner packaging, and individual pieces

Flasks

Fisherbrand Tissue Culture Flasks are available with growth areas from 12.5cm² to 300cm² and your choice of vented or plug seal caps.

- Graduated
- Writing area
- Stackable design
- Angled neck
- Resealable, self-standing packaging

Cat. No.	Capacity	Growth Area	Cap Type	Packaging
FB012933	25mL	12.5cm ²	Vent	10/Bag, 200/Case
FB012934	25mL	12.5cm ²	Plug Seal	10/Bag, 200/Case
FB012935	50mL	25cm ²	Vent	10/Bag, 200/Case
FB012936	50mL	25cm ²	Plug Seal	10/Bag, 200/Case
FB012937	250mL	75cm ²	Vent	5/Bag, 100/Case
FB012938	250mL	75cm ²	Plug Seal	5/Bag, 100/Case
FB012939	600mL	182cm ²	Vent	5/Bag, 40/Case
FB012940	600mL	182cm ²	Plug Seal	5/Bag, 40/Case
FB012941	850mL	300cm ²	Vent	3/Bag, 18/Case
FB012942	850mL	300cm ²	Plug Seal	3/Bag, 18/Case



Dishes

Fisherbrand Tissue Culture Dishes are available with growth areas from 8.5cm² to 143cm².

- Stackable lids with ventilation ribs
- Gripping ring included (except for 35mm and 150mm sizes)
- Resealable, self-standing packaging

Cat. No.	Growth Area	Dimensions (Dia. x H)	Packaging
FB012920	8.5cm ²	35 x 12mm	10/Bag, 960/Case
FB012921	21cm ²	60 x 18mm	10/Bag, 600/Case
FB012922	36cm ²	70 x 15mm	10/Bag, 600/Case
FB012923	55cm ²	90 x 17mm	10/Bag, 500/Case
FB012924	61cm ²	100 x 22mm	10/Bag, 300/Case
FB012925	143cm ²	150 x 22mm	1/Bag, 120/Case



Plates

Fisherbrand Multi-Well Tissue Culture Plates are available with 4, 6, 12, 24, 48 and 96 wells.

- Vented lids with condensation rings
- Notched plates and lids for easy orientation
- Alphanumerically labeled well
- Individually packaged (paper/plastic blister packaging)

Cat. No.	Well Volume	Growth Area	Number of Wells	Well Shape	Quantity
FB012926	2mL	2cm ²	4	Flat	100/Case
FB012927	17mL	9.5cm ²	6	Flat	100/Case
FB012928	7mL	4cm ²	12	Flat	100/Case
FB012929	3.5mL	2cm ²	24	Flat	100/Case
FB012930	1.5mL	0.8cm ²	48	Flat	100/Case
FB012931	0.4mL	0.3cm ²	96	Flat	100/Case
FB012932	0.3mL	0.3cm ²	96	Round	100/Case



© 2017 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at fishersci.com/trademarks.

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: fishersci.ca

 **fisher scientific**
part of **Thermo Fisher Scientific**