

One Click® Water Determination Simple and Secure




One Click® User Interface

The large color touchscreen features the simple-to-understand and fast-to-operate One Click user interface. All users have their own homescreen with dedicated shortcut buttons to directly start specific routine tasks.



Solvent Manager

Users are protected against contact with chemicals using the Solvent Manager liquid handling device. It is fully controlled by the titrator and offers solvent exchange with only One Click without additional user interaction.



Intelligent Burettes


The titrant is automatically recognized, when the burette is installed on the titrator. Important data such as concentration or lifetime is saved on the RFID chip and directly transferred to the titrator, where it is stored and can be monitored. Using the wrong or an expired titrant is therefore impossible.



V20S Compact Volumetric KF Titrator

The routine Karl Fischer titrator combines fast and precise water content determination with easy operation. Samples from any industry with water content between 100 ppm and 100% are analyzed in single measurements or sample series with statistics.

- Color touchscreen with One Click user interface
- User interface in English, German, French, Spanish, Italian, Chinese, Russian, Polish, Korean and Portuguese
- Intelligent burettes with RFID chip saving all relevant titrant data
- Connectivity to LabX Titration PC software via USB or direct Ethernet (TCP/IP)
- Common USB printers or the USB-P25 compact printer for secure and GLP-compliant paper recording



PC software LabX® Titration

Full control over the titrator, secure database archiving, networking, efficient result management with control charts and individual search filters or rapid and clear method development are only some aspects of the powerful LabX titration PC software.

Functionality Overview		V20S	
Application	Solid, liquid and gaseous samples	•	
	Resources and method database	•	
	KF titrants	100	
	KF standards	50	
One Click® Titration	User specific Home Screen with Shortcuts	•	
	Shortcuts per user	12	
	Solvent Control	-	
Hot Plug & Play	Solvent Manager	•	
	Burette recognition with titrant, concentration and monitoring data	•	
	External Dosing Unit for addition of auxiliary reagents	-	
	USB printer DIN-A4/US letter / USB-P25 compact printer	•	
	USB memory stick / USB barcode reader	•	
Security	LevelSens	-	
	LogStraight Fingerprint Reader	-	
Automation	InMotion KF Oven Autosamplers	-	
User Management	"Expert – Routine" user groups	•	
	Preprogrammed METTLER TOLEDO methods	-	
	KF standard methods	4	
	Max. number of user methods	5	
	External extraction/dissolution dedicated method type	-	
	Number of method function	12	
	Number of samples per series	120	
	Autostart: automatic start after sample addition	•	
	Drift stop for endpoint recognition (absolute and relative, tmax, delay)	•	
	Max. number of calculations/results per method	3	
Methods and series	User defined calculations	-	
	Statistics of up to 120 samples including result limits check, outlier test	•	
	Extra statistical functions as max. srel and multiple determinations	-	
	Recalculation of results	•	
	Data in Online Screen: time, water count, potential, stirrer speed, volume, drift	•	
	Data in measured value table: time, water count, potential, volume, drift	•	
	Curves in Online Screen and printout: E-V, E-t, V-t, drift-t, water count-t	•	
	Task list	Number of tasks queued	-
	Online Help	Context sensitive parameter explanation	•
	Data Export	USB, Ethernet, PDF	•
Languages	User interface and printouts in English, German, French, Spanish, Italian, Chinese, Russian, Polish, Korean, Portuguese	•	
PC software	LabX® Titration Express and Server	•	
Homogenizer	TTL	-	
	Ethernet (TCP/IP)	1	
Communication	COM (serial balance connection)	1	
	USB host (printer, memory stick, barcode reader, hub)	2	
	USB client (PC)	1	
	Integrated Magnetic Stirrer	1	
	Pump / Stirrer	1	

- exclusive V30S functionality

Technical Specifications

Polarized sensor input	Measurement range	-2000...+2000 mV
	Resolution / Limits of error	0.1 mV / 2 mV
	Polarization current range	0...24 µA
	Polarization current resolution / Limits of error	0.1 µA / 1 µA
Burette drive	Drive resolution	20000 steps
	Burette resolution (for 5 mL burette)	0.25 µL
	Limits of error	0.3% of the respective volume
	Resolver	32 pulses / mm stroke
	Resolver resolution	0.0625% of burette volume
	Filling time and discharge time	20 s at 100% filling rate
Environment	Ambient temperature	+5...+40 °C
	Atmospheric humidity	max. 80% at 31 °C
Titration dimensions	Width x depth x height / Weight	210 x 333 x 320 mm / 4.2 kg
	Glass beaker	150 mL
Control and display	Touchscreen	VGA 5.7" color TFT, 640 x 480 pixel
Application (depends on the environment and handling)	Drift measurement	Online, < 5 µg/min
	Measurement range	100 ppm...100%
	Repeatability	0.3% at >10 mg H ₂ O

METTLER TOLEDO

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: fishersci.ca

